# Product data sheet

Specification



Acti9 - comb busbar - 1L+N - 18 mm pitch - 57 modules - 100 A

A9XPH257

Product availability: Stock - Normally stocked in distribution facility

Price\*: 198.00 USD

### Main

Range	Acti9
Product Or Component Type	Comb busbar
Mounting Mode	Horizontal
Accessory / Separate Part Category	Connection accessory
Lines Description	1L + N
Length In 18 Mm Modules	57

### Complementary

Number Of Ways	28 ways N + 1 L
Poles Configuration For 1 Way	1 x 1P + N 1 x 2P
Connection Pitch	0.71 in (18 mm)
Connector Type	tooth
Distance Between Way	1.42 in (36 mm)
Marking	N L
Insulation	Insulated
Device Presentation	Cuttable
Provided Equipment	Set of 10 end piece
[le] Rated Operational Current	100 A 104 °F (40 °C)
[Ue] Rated Operational Voltage	415 V AC
[Ui] Rated Insulation Voltage	500 V AC IEC 61439-2
Mounting Location	Top or bottom tunnel type terminals Top or bottom double terminal
9 Mm Pitches	114
Width	39.37 in (1000 mm)
Color	White RAL 9003)
Range Compatibility	Acti 9 Acti9 iC60 Acti 9 Acti9 iK60 Acti 9 Acti9 iID Acti 9 Acti9 iID K Acti 9 Acti9 iSW Acti 9 Acti9 iSW-NA

### **Environment**

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Multi9 Multi9 C60

Standards	IEC 60947-7-1 IEC 61439-2
Fire Resistance	1760 °F (960 °C) 30 s ) IEC 60695-2-1
Pollution Degree	3 IEC 60947-7-1
Ip Degree Of Protection	IP20 with end-pieces and tooth covers

## Ordering and shipping details

Category	US10DE200908
Discount Schedule	0DE2
Gtin	3606480485138
Returnability	No
Country Of Origin	US

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.21 in (0.540 cm)
Package 1 Width	0.35 in (0.900 cm)
Package 1 Length	40.94 in (104.000 cm)
Package 1 Weight	16.05 oz (455.000 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	5
Package 2 Height	2.13 in (5.400 cm)
Package 2 Width	41.34 in (105.000 cm)
Package 2 Length	3.54 in (9.000 cm)
Package 2 Weight	5.03 lb(US) (2.280 kg)
Unit Type Of Package 3	P12
Number Of Units In Package 3	270
Package 3 Height	29.53 in (75.000 cm)
Package 3 Width	31.50 in (80.000 cm)
Package 3 Length	47.24 in (120.000 cm)
Package 3 Weight	297.89 lb(US) (135.120 kg)

### **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>Ø</b>	Reach Free Of Svhc	
<b>⊘</b>	Toxic Heavy Metal Free	
<b>⊘</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations