

Product data sheet

Specifications



Analog Converter - Input 0...10V - output 4...20 mA

ABA6TA12A

 **Discontinued on:** Jan 29, 2021

 **Discontinued**

Main

Range Of Product	Zelio Analog
Product Or Component Type	Voltage/current converter
Analogue Input Type	Current 4...20 mA Voltage 0...10 V DC
Analogue Output Type	Current 4...20 mA Voltage 0...10 V

Complementary

Abnormal Analogue Output Voltage	< 0 V
[Us] Rated Supply Voltage	24 V DC +/- 20 %, non isolated
Local Signalling	LED
Net Weight	0.10 lb(US) (0.045 kg)

Environment

Ambient Air Temperature For Storage	-40...185 °F (-40...85 °C)
-------------------------------------	----------------------------

Ordering and shipping details

Category	22375-INTERFACE MODULE(ABA,R,S)
Discount Schedule	CP2
Gtin	00785901923756
Returnability	No
Country Of Origin	DE

Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications