

# ABE9C1240C23

IP67 passive splitter box - M23 connector - with 4 channels M12 connector

Price\* : 98.00 USD



⚠ Discontinued

ABE9C1240C23 has not been replaced. Please contact your customer care center for more information.

## Main

|                           |  |
|---------------------------|--|
| Range of product          | Advantys ABE9  |
| Product or component type | IP67 passive splitter box                                      |
| Number of channels        | 4  |
| Electrical connection     | 1 male connector M23 19 pins<br>4 female connectors M12 5 pins |
| Status LED                | Without  |

## Complementary

|                       |   |
|-----------------------|---|
| Number of ways        | 8 ways  |
| System Voltage        | 24 V DC   |
| Current per channel   | <= 4 A  |
| Insulation group      | Category 3 VDE 0110   |
| Operating position    | Any position  |
| Fixing mode           | M4 screw fixing   |
| Contact resistance    | 5000 μOhm   |
| Current of common     | 16 A 0 in <sup>2</sup> (1 mm <sup>2</sup> )<br>12 A 0 in <sup>2</sup> (0.75 mm <sup>2</sup> ) |
| Separation of commons | Without   |
| Product weight        | 0.18 lb(US) (0.08 kg)   |

## Environment

|                                       |   |
|---------------------------------------|---|
| IP degree of protection               | IP67 IEC 529                                    |
| Product certifications                | CULus   |
| Ambient air temperature for operation | -4...176 °F (-20...80 °C)                       |
| Ambient air temperature for storage   | -40...185 °F (-40...85 °C)                      |
| Vibration resistance                  | 0.2 gn 57...150 Hz IEC 68-2-6, FC tests         |
| Shock resistance                      | 30 gn 11 ms EN 68-2-2<br>30 gn 11 ms IEC 68-2-2 |

## Ordering and shipping details

|          |                               |
|----------|-------------------------------|
| Category | 18218 - ADVANTYS FTB/FTM/ABE9 |
|----------|-------------------------------|

|                       |                     |
|-----------------------|---------------------|
| Discount Schedule     | PC32                |
| GTIN                  | 00785901874348      |
| Nbr. of units in pkg. | 1                   |
| Package weight(Lbs)   | 0.29999999999999999 |
| Returnability         | N                   |
| Country of origin     | DE                  |

**Contractual warranty**

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|