

Product data sheet

Characteristics

ABE9C1240L05

IP67 passive splitter box - cable 5 m - with 4 channels M12 connector

Product availability : Non-Stock - Not normally stocked in distribution facility

Price* : 99.00 USD



Main

Range of product	Advantys ABE9
Product or component type	IP67 passive splitter box
Number of channels	4
Electrical connection	1 pre-wired cable connector 16.4 ft (5 m) 4 female connectors M12 5 pins
Status LED	Without

Complementary

Number of ways	8 ways
System Voltage	24 V DC
Current per channel	<= 4 A
Insulation group	Category 3 VDE 0110
Operating position	Any position
Fixing mode	M4 screw fixing
Contact resistance	5000 µOhm
Current of common	16 A 0 in ² (1 mm ²) 12 A 0 in ² (0.75 mm ²)
Separation of commons	Without or with
Product weight	1.5 lb(US) (0.68 kg)

Environment

IP degree of protection	IP67 IEC 529
Product certifications	CULus
Ambient air temperature for operation	-4...176 °F (-20...80 °C)
Ambient air temperature for storage	-40...185 °F (-40...85 °C)
Vibration resistance	0.2 gn 57...150 Hz IEC 68-2-6, FC tests
Shock resistance	30 gn 11 ms EN 68-2-2 30 gn 11 ms IEC 68-2-2

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ordering and shipping details

Category	18218 - ADVANTYS FTB/FTM/ABE9
Discount Schedule	PC32
GTIN	00785901541660
Nbr. of units in pkg.	1
Package weight(Lbs)	2.0600000000000001
Returnability	N
Country of origin	DE

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------