

Product data sheet

Characteristics

ABL8BPK24A12

battery - 24 V DC - 75 A - 7 AH - for battery control module

Product availability : Non-Stock - Not normally stocked in distribution facility

Price* : 426.00 USD



Main

Range of product	Phaseo
Product or component type	Battery module
Input voltage	24 V DC
Output voltage	24 V DC
Maximum output current	75 A
Battery capacity	12 Ah
Holding time	< 20 hat 0.6 A, 68 °F (20 °C) > 5 minat 31.3 A, 68 °F (20 °C)

Complementary

Input voltage limits	21...29 V
Load current	1.2 A
Charging time	72 h
Output protection type	Against overload and short-circuits, protection technology: 2 x 30 A automotive type fuses
Connections - terminals	Screw type terminals input connection, connection capacity: 4 x 0.5...4 x 10 mm ² AWG 20...AWG 8 Screw type terminals output connection, connection capacity: 4 x 0.5...4 x 10 mm ² AWG 20...AWG 8
Self-discharge rate	3 %, 1 month 9 %, 3 months 15 %, 6 months
Fixing mode	By 2 screws, screw(s) Ø = 0.2 in (5 mm) on horizontal panel, operating position: horizontal By 4 screws, screw(s) Ø = 0.2 in (5 mm) on vertical panel, operating position: vertical
Output coupling	Parallel
Operating altitude	6561.68 ft (2000 m)
Service life in hours	11000 hat 104 °F (40 °C) 15000 hat 95 °F (35 °C) 22000 hat 86 °F (30 °C) 31000 hat 77 °F (25 °C) 44000 hat 68 °F (20 °C) 5000 hat 122 °F (50 °C) 7300 hat 113 °F (45 °C)
Marking	CE
Product weight	26.46 lb(US) (12 kg)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

IP degree of protection	Conforming to EN/IEC 60529
Ambient air temperature for operation	32...104 °F (0...40 °C)
Ambient air temperature for storage	-4...122 °F (-20...50 °C)
Overvoltage category	Class 3 conforming to VDE 0106-1
Vibration resistance	3.5 mm (f = 3...11.9 Hz) conforming to EN/IEC 61131-2 2 gn (f = 11.9...150 Hz) conforming to EN/IEC 61131-2
Product certifications	UL GOST

Ordering and shipping details

Category	22525 - ABL8 AND ABL7 POWER SUPPLIE
Discount Schedule	CP12
GTIN	00785901685227
Nbr. of units in pkg.	1
Package weight(Lbs)	23.01000000000002
Returnability	N
Country of origin	FR

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------