

Product data sheet

Characteristics

ACF13EC

End Closure - I-Line - end caps - 2500A max - Al/
Cu - 13.22x1.00x7.06in

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 578.00 USD



Main

Product	End Closure
Range	I-Line

Complementary

System Voltage	600 V AC/DC 50/60 Hz
Length	13.22 in
Height	7.06 in
Width	1 in
For Use with	Busbar trunking 2000 A aluminium end caps Busbar trunking 2500 A copper end caps

Environment

Standards	UL 857 IEC 61439-6 CSA C22.2 No 27 1994
-----------	---

Ordering and shipping details

Category	20199 - WALL FLANGES/END CLOSURES
Discount Schedule	PE8
GTIN	00785901816188
Nbr. of units in pkg.	1
Package weight(Lbs)	8.839999999999999
Returnability	Y
Country of origin	US

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1438 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Nickel compounds, which is known to the State of California to cause cancer, and
----- Substance 2	Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------