

Product data sheet

Characteristics

ACRC100

InRow RC, 300mm, Chilled Water, 100-120V, 50/60 Hz



ACRC100 has not been replaced. Please contact your customer care center for more information.

ⓘ Discontinued

Overview

Model Name	InRow RC, 300mm, Chilled Water, 100-120V, 50/60 Hz
Includes	Installation guide , Operations and maintenance manual
Standard Lead Time	While Supplies Last
Product Distribution	Bermuda , Brazil , Canada , Colombia , Costa Rica , Dominican Republic , Ecuador , El Salvador , Guatemala , Honduras , Japan , Mexico , Netherlands Antilles , Nicaragua , Panama , Peru , Puerto Rico , Trinidad And Tobago , United States , Venezuela

General

Air Discharge Patterns	Horizontal
Intake Air	Rear Return
Air Flow	2900.0
Minimum Water Inlet Temperature	45.0
Condensate Pump Capacity	1.3

Input

Number of Power Cords	2
Nominal Input Voltage	100V , 120V
Input Power	1100 W
Input Frequency	50/60 Hz
Rack Height	42 U
Input Connections	NEMA L5-20P

Communications & Management

Control panel	Multi-function LCD status and control console
Audible Alarm	Audible and visible alarms prioritized by severity

Physical

Maximum Height	78.41 inches (1991.0 mm)
Maximum Width	11.8 inches (300.0 mm)
Maximum Depth	42.14 inches (1070.0 mm)
Net Weight	358.0 lbs (162.73 kg)

Shipping Weight	425.5 lbs (193.42 kg)
Shipping Height	83.4 inches (2118.0 mm)
Shipping Width	29.38 inches (746.0 mm)
Shipping Depth	44.76 inches (1137.0 mm)
Color	Black
Units per Pallet	1.0

Conformance

Approvals	FCC Part 15 Class A , ICES-003 , Industry Canada , MEA , UL Listed , VCCI , cUL Listed
Standard warranty	1 year (parts only) , 1 year on-site repair or replace with factory authorized Start-Up

Sustainable Offer Status

Other Environmental Compliance	China RoHS
--------------------------------	------------