

# Product data sheet

Specifications



## FIXING SCREW

AF1VA618

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 0.42 USD

### Main

Accessory / Separate Part Category	Mounting accessories
Quantity Per Set	Set of 100
Star-Delta Starter Component	1/4 turn sliding clip nuts and corresponding bolts Screw with captive washer

### Complementary

Assembly Style	For assembly
Fixing Of Mechanism	Screws
Head Mounting	M6 x 18
Iso Thread	M6
Motor Power Kw	15 kW 200 kW 250 kW 280 kW 315 kW 4 kW 5.5 kW 55 kW 7.5 kW 11 kW 110 kW 132 kW 100 kW 147 kW 22 kW 220 kW 25 kW 59 kW 75 kW 90 kW 18.5 kW 37 kW 160 kW 185 kW 30 kW 375 kW 63 kW
Motor Starter Type	Star-delta starters
Mounting Support	Combination AM1-ED rail Omega AM1-DE rail Omega AM1-DP rail Asymmetrical DZ5-MB rail Notched AM1-EC rail
Number Of Devices	12 2 8 15
Product Compatibility	For uprights AM3-EC

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Product Mounting	Rail Mounting plate
Net Weight	0.01 lb(US) (0.006 kg) 0.01 lb(US) (0.005 kg)
Shape Of Screw Head	Slotted hexagonal
Star-Delta Mechanical Interlock	Without
Threaded Length	0.71 in (18 mm)
Provided Equipment	Washer

## Ordering and shipping details

Category	US10I1122626
Discount Schedule	0I11
Gtin	3389110570229
Returnability	Yes
Country Of Origin	IT

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.39 in (1.000 cm)
Package 1 Width	0.39 in (1.000 cm)
Package 1 Length	0.98 in (2.500 cm)
Package 1 Weight	0.21 oz (6.000 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	100
Package 2 Height	0.79 in (2.000 cm)
Package 2 Width	4.33 in (11.000 cm)
Package 2 Length	5.71 in (14.500 cm)
Package 2 Weight	21.83 oz (619.000 g)
Unit Type Of Package 3	S02
Number Of Units In Package 3	1600
Package 3 Height	5.91 in (15.000 cm)
Package 3 Width	11.81 in (30.000 cm)
Package 3 Length	15.75 in (40.000 cm)
Package 3 Weight	22.26 lb(US) (10.095 kg)

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
Reach Regulation		<a href="#">REACH Declaration</a>
Eu Rohs Directive		Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation		<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)