



Price\*\* : 2,368.00 USD



### Main

Product or component type	Straight length
Range of product	I-Line

### Complementary

Line Rated Current	1200 A
Short Circuit Rating	50 kA
Busbar Material	Aluminium busbar
Integral Ground	50 percent capacity integral ground bus
Rated Voltage	600 V AC
Number of Phases	3 phases
Wiring configuration	3-wire
Length	457.20 mm (18 in)

### Environment

Product certifications	UL listed file E22182
Standards	CSA C22.2 No 27:1997 IEC 61439-2 UL 857

### Ordering and shipping details

Category	20256-AF2/AFH2 1200A 3WIRE-COMM
Discount Schedule	PE8
GTIN	00785901284741
Package weight(Lbs)	27.45 lb(US) (12.451 kg)
Returnability	No
Country of origin	US

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds and Bisphenol A (BPA) which is known to the State of California to cause Carcinogen + Reproductive harm. For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Under investigation
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

## Contractual warranty

Warranty	18 months
----------	-----------