

Product data sheet

Characteristics

AF2312G6ST

BUSWAY STRAIGHT LENGTH 6FT 1200A INDOOR

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 3,552.00 USD



Main

Product or component type	Straight length
Range of product	I-Line

Complementary

Line Rated Current	1200 A
Short Circuit Rating	50 kA
Busbar Material	Aluminium busbar
Integral Ground	50 percent capacity integral ground bus
System Voltage	600 V AC
Phase	3 phases
Wiring configuration	3-wire
Length	6 ft

Environment

Product certifications	UL listed file E22182
Standards	IEC 61439-2 UL 857 CSA C22.2 No 27 1997

Ordering and shipping details

Category	20256 - AF2/AFH2 1200A 3WIRE-COMM
Discount Schedule	PE8
GTIN	00785901767282
Nbr. of units in pkg.	1
Package weight(Lbs)	71
Returnability	N

Country of origin	US
-------------------	----

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1438 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Nickel compounds, which is known to the State of California to cause cancer, and
----- Substance 2	Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------