

# Product data sheet

## Characteristics

# AF2316G10FES

Flanged End - I-Line - 1600A - 3W - Al -  
10.00x18.82x13.88in

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 2,902.00 USD



### Main

Product	Flanged end
Range	I-Line

### Complementary

Rated Current	1600 A, for aluminium
System Voltage	600 V AC/DC 50/60 Hz
Length	10 in
Height	13.88 in
Width	18.82 in
Material	Aluminium busbar
I-LINE Value End	Slot
Phase	3 phases
For Use with	Busbar trunking 1600 A aluminium
Protection Type	50 percent capacity integral ground bus
Wiring Configuration	3-wire

### Environment

Standards	UL 857 IEC 61439-6 CSA C22.2 No 27 1994
-----------	---

### Ordering and shipping details

Category	20260 - AF2/AFH2 1600A 3WIRE-COMM
Discount Schedule	PE8
GTIN	00785901015697
Nbr. of units in pkg.	1

Package weight(Lbs)	52.64000000000001
Returnability	Y
Country of origin	US

**Offer Sustainability**

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Nickel compounds, which is known to the State of California to cause cancer, and
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

**Contractual warranty**

Warranty period	18 months
-----------------	-----------