

Product data sheet

Characteristics

AF2316GLFM13

Busway - I-Line - elbow - 1600A - 3W - grd - flat - Al - 13x13in

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 3,782.00 USD



Main

Product or Component Type	Elbow
Range	I-Line

Complementary

Rated Current	1600 A
Busbar Material	Aluminium busbar
Busbar Position	Flat
Integral Ground	50 percent capacity integral ground bus
System Voltage	600 V AC
Phase	3 phases
Wiring Configuration	3-wire
Length	13 in
Width	13 in

Ordering and shipping details

Category	20260 - AF2/AFH2 1600A 3WIRE-COMM
Discount Schedule	PE8
GTIN	00785901807667
Nbr. of units in pkg.	1
Package weight(Lbs)	42
Returnability	Y
Country of origin	US

Offer Sustainability

Sustainable offer status	Green Premium product
--------------------------	-----------------------

RoHS (date code: YYWW)	Compliant - since 1438 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Nickel compounds, which is known to the State of California to cause cancer, and
----- Substance 2	Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------