

Product data sheet

Characteristics

AF2320G10ST

BUSWAY STRAIGHT LENGTH 10FT 2000A INDOOR

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 10,040.00 USD



Main

Product or component type	Straight length
Range of product	I-Line

Complementary

Line Rated Current	2000 A
Short Circuit Rating	100 kA
Busbar Material	Aluminium busbar
Integral Ground	50 percent capacity integral ground bus
System Voltage	600 V AC
Phase	3 phases
Wiring configuration	3-wire
Length	10 ft

Environment

Product certifications	UL listed file E22182
Standards	IEC 61439-2 UL 857 CSA C22.2 No 27 1997

Ordering and shipping details

Category	20261 - AF2/AFH2 2000A 3WIRE-INDL
Discount Schedule	PE8
GTIN	00785901329817
Nbr. of units in pkg.	1
Package weight(Lbs)	165
Returnability	Y

Country of origin	US
-------------------	----

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1438 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Nickel compounds, which is known to the State of California to cause cancer, and
----- Substance 2	Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------