

Product data sheet

Characteristics

AF2508GETBMB

End Tap Box - I-Line - 800A - 4W - Al - Bolt -
29.14x11.00x28.00in

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 5,408.00 USD



Main

Product	End tap box
Range	I-Line

Complementary

Rated Current	800 A, for aluminium
System Voltage	600 V AC/DC 50/60 Hz
Length	29.14 in
Height	28 in
Width	11 in
Material	Aluminium busbar
I-LINE Value End	Bolt
Phase	3 phases
For Use with	Busbar trunking 800 A aluminium
Protection Type	50 percent capacity integral ground bus
Wiring Configuration	4-wire

Environment

Standards	UL 857 IEC 61439-6 CSA C22.2 No 27 1994
-----------	---

Ordering and shipping details

Category	20002 - AF2/AFH2 800A 4WIRE-COMM
Discount Schedule	PE8
GTIN	00785901815853
Nbr. of units in pkg.	1

Package weight(Lbs)	130
Returnability	Y
Country of origin	US

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1438 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Nickel compounds, which is known to the State of California to cause cancer, and
----- Substance 2	Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------