

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 4,000.00 USD



Main

Product or component type	Straight length
Range of product	I-Line

Complementary

Line Rated Current	1600 A
Short Circuit Rating	50 kA
Busbar Material	Aluminium busbar
Integral Ground	50 percent capacity integral ground bus
System Voltage	600 V AC
Phase	3 phases
Wiring configuration	4-wire
Length	18 in

Environment

Product certifications	UL listed file E22182
Standards	IEC 61439-2 UL 857 CSA C22.2 No 27 1997

Ordering and shipping details

Category	20010 - 1600A AL FEEDER BUS IP54 THERMAL
Discount Schedule	PE8
GTIN	00785901564812
Nbr. of units in pkg.	1
Package weight(Lbs)	0.01
Returnability	N
Country of origin	US

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Nickel compounds, which is known to the State of California to cause cancer, and
----- Substance 2	Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------