

# Product data sheet

## Characteristics

# AF2530G10ST

## BUSWAY STRAIGHT LENGTH 10FT 3000A INDOOR

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 17,440.00 USD



### Main

Product or component type	Straight length
Range of product	I-Line

### Complementary

Line Rated Current	3000 A
Short Circuit Rating	100 kA
Busbar Material	Aluminium busbar
Integral Ground	50 percent capacity integral ground bus
System Voltage	600 V AC
Phase	3 phases
Wiring configuration	4-wire
Length	10 ft

### Environment

Product certifications	UL listed file E22182
Standards	IEC 61439-2 UL 857 CSA C22.2 No 27 1997

### Ordering and shipping details

Category	20015 - AF2/AFH2 3000A 4WIRE-INDL
Discount Schedule	PE8
GTIN	00785901060376
Nbr. of units in pkg.	1
Package weight(Lbs)	282.15000000000003
Returnability	N

Country of origin	US
-------------------	----

**Offer Sustainability**

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1438 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Nickel compounds, which is known to the State of California to cause cancer, and
----- Substance 2	Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

**Contractual warranty**

Warranty period	18 months
-----------------	-----------