

Product data sheet

Characteristics

AFH2516GCTB

Tap Box - I-Line - 1600A - 4W - Al -
48.00x35.00x28.00in

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 11,076.00 USD



Main

Product	Tap box
Range	I-Line

Complementary

Rated Current	1600 A, for aluminium
System Voltage	600 V AC/DC 50/60 Hz
Length	48 in
Height	28 in
Width	35 in
Material	Aluminium busbar
I-LINE Value End	Bolt
Phase	3 phases
Protection Type	50 percent capacity integral ground bus High short-circuit bracing
Wiring Configuration	4-wire

Environment

Standards	UL 857 IEC 61439-6 CSA C22.2 No 27 1994
-----------	---

Ordering and shipping details

Category	20010 - 1600A AL FEEDER BUS IP54 THERMAL
Discount Schedule	PE8
GTIN	00785901284727
Nbr. of units in pkg.	1

Package weight(Lbs)	300.43000000000001
Returnability	Y
Country of origin	US

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Nickel compounds, which is known to the State of California to cause cancer, and
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------