

Product data sheet

Specifications

Cable duct - 90 x 30 mm - without cover - blue



AK2GA39

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 54.00 USD

Main

Product Or Component Type	Cable duct
Accessory / Separate Part Category	Cabling accessories
Range Compatibility	Spacial S3D Spacial CRN Thalassa PLA Thalassa PLS Thalassa PLM
Device Composition	Without cover
Quantity Per Set	Set of 8

Complementary

Color	Blue RAL 5000)
Fixing Mode	By screws Clip-on support
Material	PVC (polyvinyl chloride)
Height	3.54 in (90 mm)
Length	78.74 in (2000 mm)
Width	1.18 in (30 mm)
Net Weight	2.47 lb(US) (1.12 kg)
Total Number Of Wires	200

Environment

Ambient Air Temperature For Operation	23...140 °F (-5...60 °C)
Flame Retardance	V-0 UL 94
Fire Resistance	1760 °F (960 °C) IEC 60695-2-1/1
Standards	VDE 0506 DIN 43659 NF C 68-102 VDE 0660

Ordering and shipping details

Category	US1000I22622
Discount Schedule	000I
Gtin	3389110570274
Returnability	No

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Country Of Origin	FR
-------------------	----

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.28 in (18.5 cm)
Package 1 Width	3.35 in (8.5 cm)
Package 1 Length	78.74 in (200.0 cm)
Package 1 Weight	3.69 lb(US) (1.675 kg)
Unit Type Of Package 2	CAR
Number Of Units In Package 2	8
Package 2 Height	3.35 in (8.5 cm)
Package 2 Width	7.28 in (18.5 cm)
Package 2 Length	78.74 in (200.0 cm)
Package 2 Weight	29.54 lb(US) (13.4 kg)
Unit Type Of Package 3	P2M
Number Of Units In Package 3	336
Package 3 Height	47.24 in (120 cm)
Package 3 Width	79.53 in (202 cm)
Package 3 Length	27.56 in (70 cm)
Package 3 Weight	518.09 lb(US) (235 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability





Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Reach Regulation		REACH Declaration
Eu Rohs Directive		Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation		China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)