

Price* : 122.00 USD



AK5PA2312 has not been replaced. Please contact your customer care center for more information.

ⓘ Discontinued

Main

Range	Linergy
Product name	HK
Product or component type	Mounting plate
Poles description	3P + Nc
[I _{th}] conventional free air thermal current	25 A
I ² t on activation	200000 A ² .s
Number of cables	1 cable(s) 0 in ² (1.5 mm ²) 3 cable(s) 0.01 in ² (4 mm ²) at 221 °F (105 °C)
Width	2.13 in (54 mm)
Height	7.48 in (190 mm)
Depth	2.4 in (61 mm)

Complementary

[U _i] rated insulation voltage	690 V conforming to IEC 60439-1
9 mm pitches	6
Product weight	0.52 lb(US) (0.235 kg)

Environment

Standards	IEC 60439
Product certifications	CSA DNV LROS (Lloyds register of shipping) UL

Ordering and shipping details

Category	22623 - PANEL BUS (AK5)
Discount Schedule	I11
Nbr. of units in pkg.	1
Package weight(Lbs)	0.8399999999999997
Returnability	N
Country of origin	FR

Contractual warranty

Warranty period	18 months
-----------------	-----------
