

Product data sheet

Specifications



Mounting plate, Linergy HK, 3P+Nc, 25A, 190x54x61mm

AK5PA2312S

⚠ Discontinued

Main

Range	Linergy
Product Name	HK
Product Or Component Type	Mounting plate
Poles Description	3P + Nc
[Ith] Conventional Free Air Thermal Current	25 A
I²T On Activation	200000 A².s
Number Of Cables	3 0.01 in² (4 mm²) 221 °F (105 °C) 1 0.00 in² (1.5 mm²)
Width	4.17 in (106 mm)
Height	7.48 in (190 mm)
Depth	2.48 in (63 mm)

Complementary

[Ui] Rated Insulation Voltage	690 V IEC 60439-1
9 Mm Pitches	12
Net Weight	1.34 lb(US) (0.61 kg)

Environment

Standards	IEC 60439
Product Certifications	LROS (Lloyds register of shipping) DNV UL CSA

Ordering and shipping details

Category	22623-PANEL BUS (AK5)
Discount Schedule	I11
Gtin	3389110576948
Returnability	No

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	3.58 in (9.100 cm)
Package 1 Width	4.53 in (11.500 cm)
Package 1 Length	9.37 in (23.800 cm)
Package 1 Weight	28.78 oz (815.900 g)
Unit Type Of Package 2	S03
Number Of Units In Package 2	9
Package 2 Height	11.81 in (30.000 cm)
Package 2 Width	11.81 in (30.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	17.44 lb(US) (7.910 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability





Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Reach Free Of Svhc	
 Toxic Heavy Metal Free	
 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.