

# Product data sheet

Specifications



Plug outlet, Linergy HK, 3P+Nc,  
16A, 2 points, cable length 200

AK5PC131

! Discontinued

## Main

Range	Linergy
Product Name	HK
Product Or Component Type	Plug outlet
Poles Description	3P + Nc
[Ith] Conventional Free Air Thermal Current	10 A common mode 16 A
I²T On Activation	100000 A².s
Number Of Points	2
Number Of Cables	1 0.00 in² (1.5 mm²) 3 0.00 in² (2.5 mm²)
Cable Length	0.66 ft (0.2 m)
Quantity Per Set	Set of 6

## Complementary

[Ui] Rated Insulation Voltage	600 V CSA 600 V UL 690 V IEC 60439-1
Peak Current	25 kA
Electrical Connection	Connector
Width	1.42 in (36 mm)
Height	1.81 in (46 mm)
Depth	1.50 in (38 mm)
Net Weight	0.10 lb(US) (0.045 kg)

## Environment

Standards	IEC 60439
Product Certifications	DNV LROS (Lloyds register of shipping) UL CSA

## Ordering and shipping details

Category	22623-PANEL BUS (AK5)
Discount Schedule	I11

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Gtin	3389110576832
Returnability	No

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.92 in (12.5 cm)
Package 1 Width	5.12 in (13.0 cm)
Package 1 Length	6.10 in (15.5 cm)
Package 1 Weight	1.90 oz (54.0 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	6
Package 2 Height	4.92 in (12.5 cm)
Package 2 Width	5.12 in (13.0 cm)
Package 2 Length	6.10 in (15.5 cm)
Package 2 Weight	13.79 oz (391.0 g)
Unit Type Of Package 3	S04
Number Of Units In Package 3	90
Package 3 Height	11.81 in (30.0 cm)
Package 3 Width	15.75 in (40.0 cm)
Package 3 Length	23.62 in (60.0 cm)
Package 3 Weight	15.56 lb(US) (7.06 kg)

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
Reach Regulation		<a href="#">REACH Declaration</a>
Eu Rohs Directive		Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation		<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)