

# Product data sheet

Specifications



Plug outlet, Linergy HK, 3P+N, 32A,  
2 points, 4mm<sup>2</sup>, cable length  
1000mm

AK5PC34L

! Discontinued

## Main

Range	Linergy
Product Name	HK
Product Or Component Type	Plug outlet
Poles Description	3P + N
[Ith] Conventional Free Air Thermal Current	32 A
I²T On Activation	200000 A².s
Number Of Points	2
Number Of Cables	4 0.01 in² (4 mm²)
Cable Length	3.28 ft (1 m)
Quantity Per Set	Set of 6

## Complementary

[Ui] Rated Insulation Voltage	600 V CSA 600 V UL 690 V IEC 60439-1
Peak Current	25 kA
Width	1.42 in (36 mm)
Height	1.81 in (46 mm)
Depth	1.50 in (38 mm)
Net Weight	0.14 lb(US) (0.065 kg)

## Environment

Standards	IEC 60439
Product Certifications	UL CSA DNV LROS (Lloyds register of shipping)

## Ordering and shipping details

Category	22623-PANEL BUS (AK5)
Discount Schedule	I11
Gtin	3389110576887
Returnability	No

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Country Of Origin	FR
-------------------	----

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.43 in (8.7 cm)
Package 1 Width	9.17 in (23.3 cm)
Package 1 Length	9.49 in (24.1 cm)
Package 1 Weight	7.27 oz (206 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	6
Package 2 Height	3.43 in (8.7 cm)
Package 2 Width	9.49 in (24.1 cm)
Package 2 Length	9.17 in (23.3 cm)
Package 2 Weight	2.73 lb(US) (1.24 kg)
Unit Type Of Package 3	S04
Number Of Units In Package 3	54
Package 3 Height	11.81 in (30 cm)
Package 3 Width	15.75 in (40 cm)
Package 3 Length	23.62 in (60 cm)
Package 3 Weight	26.60 lb(US) (12.067 kg)

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability





**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Reach Regulation	<a href="#">REACH Declaration</a>	
Eu Rohs Directive	Compliant	<a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.	