

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 139.00 USD



Main

Range of product	L525
Series name	Severe duty
Product or component type	Limit switch lever
Device short name	L525
Associated complete product	L525
Movement of operating head	Rotary
Type of operator	Aluminium spring return roller pin lever length: 5.73 in belt conveyor monitoring cylindrical roller pin
Type of roller	1 teflon lateral roller diameter: 1.25 in
Type of approach	Lateral approach
Positive opening	Without

Complementary

Switch actuation	By shifting conveyor belt
Product weight	0.1 lb(US)

Environment

Ambient air temperature for operation	-20...185 °F
Ambient air temperature for storage	-20...185 °F
Environmental characteristic	Standard environment

Ordering and shipping details

Category	21519 - 9007 MISCELLANEOUS
Discount Schedule	DS1
GTIN	00785901773429
Nbr. of units in pkg.	1
Package weight(Lbs)	0.10000000000000001

Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and
----- Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------