Product data sheet

Specifications



Busway, I-Line, elbow, 600A, 4 wire, front out, horizontal,

Price*: 2,994.00 USD

Main

Product Or Component Type	Elbow
Range	I-Line

Complementary

Rated Current	600 A
Busbar Material	Aluminium: busbar
Integral Ground	Without protection
Rated Operational Voltage	600 V AC
Number Of Phases	3 phase
Wiring Configuration	4-wire
Position	Front outside
Orientation	Horizontal
Length	18 in (457.20 mm)
Width	18 in (457.20 mm)

Ordering and shipping details

Category	20063-AP 600A 4WIRE-COMM
Discount Schedule	PE8
Returnability	No
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	42.17 lb(US) (19.128 kg)

Contractual warranty

Warranty

18 months

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Pvc Free

Certifications & Standards

REACh Declaration
Compliant
EU RoHS Declaration
China RoHS declaration
Pro-active China RoHS declaration (out of China RoHS legal scope)
Product Environmental Profile
No need of specific recycling operations
WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov