



Overview

Model Name	APC 16 Port Multi-Platform Analog KVM
Includes	C13-C14 power cord , Configuration cable , Documentation CD , Firmware upgrade cable , KVM cables not included , NEMA 5-15 power cord , Rack Mounting brackets , User Manual
Standard Lead Time	Usually in Stock
Product Distribution	Afghanistan , Albania , Algeria , Andorra , Angola , Anguilla , Antigua And Barbuda , Argentina , Armenia , Aruba , Australia , Austria , Azerbaijan , Bahrain , Bangladesh , Barbados , Belarus , Belgium , Belize , Benin , Bermuda , Bhutan , Bolivia , Bosnia And Herzegovina , Botswana , Brazil , Brunei Darussalam , Bulgaria , Burkina Faso , Burundi , Cambodia , Cameroon , Canada , Cayman Islands , Central African Republic , Chad , Chile , China , Colombia , Congo , CONGO, THE DEMOCRATIC REPUBLIC OF THE , Cook Islands , Costa Rica , Cote D'Ivoire , Croatia , Cuba , Cyprus , Czech Republic , Denmark , Djibouti , Dominican Republic , East Timor , Ecuador , Egypt , El Salvador , Equatorial Guinea , Eritrea , Estonia , Ethiopia , Falkland Islands (Malvinas) , Fiji , Finland , France , Gabon , Gambia , Georgia , Germany , Ghana , Gibraltar , Greece , Guatemala , Guinea , Guyana , Honduras , Hong Kong , Hungary , Iceland , India , Indonesia , Iran (Islamic Republic Of) , Iraq , Ireland , Israel , Italy , Jamaica , Japan , Jordan , Kazakhstan , Kenya , KOREA, REPUBLIC OF , Kuwait , Latvia , Lebanon , Lesotho , Liberia , Liechtenstein , Lithuania , Luxembourg , Macedonia , Malawi , Malaysia , Mali , Malta , Mauritania , Mexico , Moldova, Republic Of , Mongolia , Morocco , Mozambique , Myanmar , Namibia , Nepal , Netherlands , Netherlands Antilles , New Zealand , Nicaragua , Niger , Nigeria , Norway , Oman , Pakistan , Panama , Papua New Guinea , Paraguay , Peru , Philippines , Poland , Portugal , Puerto Rico , Romania , Russian Federation , Rwanda , Saudi Arabia , Senegal , Sierra Leone , Singapore , Slovakia (Slovak Republic) , Slovenia , Somalia , South Africa , Spain , Sri Lanka , Sudan , Suriname , Sweden , Switzerland , Taiwan , Tajikistan , TANZANIA, UNITED REPUBLIC OF , Thailand , Togo , Trinidad And Tobago , Tunisia , Turkey , Turkmenistan , Uganda , Ukraine , United Arab Emirates , United States , Uruguay , Uzbekistan , Venezuela , Viet Nam , VIRGIN ISLANDS (UNITED STATES) , Western Sahara , Yemen , Zambia , Zimbabwe

Input

Input Frequency	50/60 Hz
-----------------	----------

Physical

Net Weight	10.0 lbs (4.55 kg)
Maximum Height	1.75 inches (44.0 mm)
Maximum Width	17.0 inches (432.0 mm)
Maximum Depth	8.25 inches (210.0 mm)
Shipping Weight	11.0 lbs (5.0 kg)
Shipping Height	5.0 inches (127.0 mm)
Shipping Width	20.0 inches (508.0 mm)

Shipping Depth	13.0 inches (330.0 mm)
Rack Height	1 U
Color	Black

Environmental

Operating Environment	32 - 122 °F (0 - 50 °C)
Operating Relative Humidity	0 - 85 %
Storage Temperature	-4 - 122 °F (-20 - 50 °C)

Conformance

Approvals	AS/NZS 3548 (C-Tick) Class A , CE , FCC Part 15 Class A , ICES-003 , TAA compliance , UL 60950 , VCCI
Standard warranty	2 years repair or replace

Sustainable Offer Status

RoHS	Compliant
------	-----------