



Overview

Description	1U rack-mountable keyboard, mouse, and LCD console with US English keyboard layout.
Model Name	APC 19" Rack LCD Console
Includes	C13-C14 power cord , Documentation CD , Firmware upgrade cable , Installation guide , NEMA 5-15 power cord , PS2 KVM cable , Rack mounting hardware , Single user rack mount kit , USB KVM cable , USB cable
Standard Lead Time	Usually in Stock
Product Distribution	Afghanistan , Albania , Algeria , Andorra , Angola , Anguilla , Antigua And Barbuda , Argentina , Armenia , Aruba , Australia , Austria , Azerbaijan , Bahamas , Bahrain , Bangladesh , Barbados , Belarus , Belgium , Belize , Benin , Bermuda , Bhutan , Bolivia , Bosnia And Herzegovina , Botswana , Brazil , Brunei Darussalam , Bulgaria , Burkina Faso , Burundi , Cameroon , Canada , Cayman Islands , Central African Republic , Chad , Chile , Colombia , Congo , CONGO, THE DEMOCRATIC REPUBLIC OF THE , Cook Islands , Costa Rica , Cote D'Ivoire , Croatia , Cuba , Cyprus , Czech Republic , Denmark , Djibouti , Dominica , Dominican Republic , East Timor , Ecuador , Egypt , El Salvador , Equatorial Guinea , Eritrea , Estonia , Ethiopia , Falkland Islands (Malvinas) , Fiji , Finland , France , Gabon , Gambia , Georgia , Germany , Ghana , Gibraltar , Greece , Grenada , Guadeloupe , Guatemala , Guinea , Guyana , French Guiana , Haiti , Honduras , Hungary , Iceland , India , Indonesia , Iran (Islamic Republic Of) , Iraq , Ireland , Israel , Italy , Jamaica , Japan , Jordan , Kazakhstan , Kenya , KOREA, REPUBLIC OF , Kuwait , Latvia , Lebanon , Lesotho , Liberia , Liechtenstein , Lithuania , Luxembourg , Macedonia , Madagascar , Malawi , Malaysia , Mali , Malta , Martinique , Mauritania , Mauritius , Mayotte , Mexico , Moldova, Republic Of , Mongolia , Morocco , Mozambique , Myanmar , Namibia , Nepal , Netherlands , Netherlands Antilles , New Zealand , Nicaragua , Niger , Nigeria , Norway , Oman , Pakistan , Panama , Papua New Guinea , Paraguay , Peru , Philippines , Poland , Portugal , Puerto Rico , Reunion , Romania , Russian Federation , Rwanda , SAINT KITTS AND NEVIS , SAINT LUCIA , SAINT VINCENT AND THE GRENADINES , Saudi Arabia , Senegal , Sierra Leone , Singapore , Slovakia (Slovak Republic) , Slovenia , Somalia , South Africa , Spain , Sri Lanka , Sudan , Suriname , Sweden , Switzerland , Taiwan , Tajikistan , TANZANIA, UNITED REPUBLIC OF , Thailand , Togo , Trinidad And Tobago , Tunisia , Turkey , Turkmenistan , Turks And Caicos Islands , Uganda , Ukraine , United Arab Emirates , United States , Uruguay , Uzbekistan , Venezuela , Viet Nam , VIRGIN ISLANDS (UNITED STATES) , Western Sahara , Yemen , Zambia , Zimbabwe

Input

Nominal Input Voltage	100V , 240V
Input Frequency	50/60 Hz

Supported Hardware

Panel Size	19
Pixel Pitch	0.26

Trackball Type	PS/2 Touchpad , USB mouse
LCD Power Consumption	19 W

## Physical

Net Weight	38.28 lbs (17.4 kg)
Maximum Height	1.73 inches (44.0 mm)
Maximum Width	18.97 inches (482.0 mm)
Maximum Depth	26.18 inches (665.0 mm)
Shipping Weight	46.17 lbs (20.99 kg)
Shipping Height	6.0 inches (152.0 mm)
Shipping Width	26.5 inches (673.0 mm)
Shipping Depth	32.5 inches (826.0 mm)
Minimum Mounting Depth	26.77
Maximum Mounting Depth	41.33
Rack Height	1 U
Color	Black

## Environmental

Operating Environment	32 - 104 °F (0 - 40 °C)
-----------------------	-------------------------

## Conformance

Approvals	C-tick , CE , EN 55022 Class A , EN 55024 , EN 60950 , FCC Part 15 Class A , IEC 60950 , Industry Canada , KCC , NOM , UL Listed , VCCI Class A , VDE
Standard warranty	2 years repair or replace

## Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs