

# AP5822

## APC Integrated Rack LCD/KVM USB Cable - 10ft (3m)



### Overview

|                      |  |
|----------------------|--|
| Model Name           | APC Integrated Rack LCD/KVM USB Cable - 10ft (3m)  |
| Standard Lead Time   | Usually in Stock   |
| Product Distribution | Afghanistan , Albania , Algeria , Andorra , Angola , Armenia , Australia , Austria , Azerbaijan , Bahrain , Bangladesh , Belarus , Belgium , Benin , Bhutan , Bosnia And Herzegovina , Botswana , Brunei Darussalam , Bulgaria , Burkina Faso , Burundi , Cambodia , Cameroon , Canada , Cayman Islands , Central African Republic , Chad , China , Congo , CONGO, THE DEMOCRATIC REPUBLIC OF THE , Cook Islands , Cote D'Ivoire , Croatia , Cyprus , Czech Republic , Denmark , Djibouti , East Timor , Egypt , Equatorial Guinea , Eritrea , Estonia , Ethiopia , Fiji , Finland , France , Gabon , Gambia , Georgia , Germany , Ghana , Gibraltar , Greece , Guinea , Hong Kong , Hungary , Iceland , India , Indonesia , Iran (Islamic Republic Of) , Iraq , Ireland , Israel , Italy , Japan , Jordan , Kazakhstan , Kenya , KOREA, REPUBLIC OF , Kuwait , Latvia , Lebanon , Lesotho , Liberia , Liechtenstein , Lithuania , Luxembourg , Macedonia , Malawi , Malaysia , Mali , Malta , Mauritania , Moldova, Republic Of , Mongolia , Morocco , Mozambique , Myanmar , Namibia , Nepal , Netherlands , New Zealand , Niger , Nigeria , Norway , Oman , Pakistan , Papua New Guinea , Philippines , Poland , Portugal , Romania , Russian Federation , Rwanda , Saudi Arabia , Senegal , Sierra Leone , Singapore , Slovakia (Slovak Republic) , Slovenia , Somalia , South Africa , Spain , Sri Lanka , Sudan , Suriname , Sweden , Switzerland , Taiwan , Tajikistan , TANZANIA, UNITED REPUBLIC OF , Thailand , Togo , Tunisia , Turkey , Turkmenistan , Uganda , Ukraine , United Arab Emirates , United States , Uzbekistan , Viet Nam , VIRGIN ISLANDS (UNITED STATES) , Western Sahara , Yemen , Zambia , Zimbabwe |

### Physical

|                 |                            |
|-----------------|----------------------------|
| Net Weight      | 0.31 lbs (0.15 kg)         |
| Maximum Height  | 0.5 inches (13.0 mm)       |
| Maximum Width   | 1.0 inches (25.0 mm)       |
| Maximum Depth   | 0.5 inches (13.0 mm)       |
| Shipping Weight | 0.34 lbs (0.15 kg)         |
| Shipping Height | 1.97 inches (50.0 mm)      |
| Shipping Width  | 6.5 inches (165.0 mm)      |
| Shipping Depth  | 9.25 inches (235.0 mm)     |
| Cord Length     | 12 feet (3.66 meters)      |
| Connector A     | USB-A(USB 2.0)             |
| Connector B     | HighDensity15(VGA Monitor) |
| Mount Positions | Hidden                     |

Conformance

---

|                   |                           |
|-------------------|---------------------------|
| Standard warranty | 2 years repair or replace |
|-------------------|---------------------------|

---

Sustainable Offer Status

---

|       |                          |
|-------|--------------------------|
| RoHS  | Compliant                |
| REACH | REACH: Contains No SVHCs |

---