



Overview

| | |
|----------------------|--|
| Model Name | Rack PDU, Basic, 0U/1U, 208V, 30A, (4) C19 |
| Includes | Installation guide , Safety guide |
| Standard Lead Time | Usually in Stock |
| Product Distribution | Afghanistan , Australia , Bangladesh , Bhutan , Brunei Darussalam , Cambodia , Canada , China , Cook Islands , East Timor , Fiji , Hong Kong , India , Indonesia , KOREA, REPUBLIC OF , Malaysia , Myanmar , Nepal , New Zealand , Papua New Guinea , Philippines , Singapore , Sri Lanka , Taiwan , Thailand , United States , Viet Nam |

Output

| | |
|--------------------------------------|----------------------------------|
| Nominal Output Voltage | 200V , 208V |
| Maximum Total Current Draw per Phase | 30 A |
| Output Connections | (4) IEC 320 C19 (Battery Backup) |
| Overload Protection | Yes |

Input

| | |
|--|-----------------------|
| Nominal Input Voltage | 200V , 208V |
| Input Frequency | 50/60 Hz |
| Regulatory Derated Input Current (North America) | 24 A |
| Input Connections | NEMA L6-30P |
| Cord Length | 12 feet (3.66 meters) |
| Maximum Line Current per phase | 30 A |
| Maximum Input Current per phase | 30 A |

Physical

| | |
|-----------------|-------------------------|
| Net Weight | 8.36 lbs (3.8 kg) |
| Maximum Height | 1.72 inches (44.0 mm) |
| Maximum Width | 17.25 inches (438.0 mm) |
| Maximum Depth | 4.95 inches (126.0 mm) |
| Shipping Weight | 10.12 lbs (4.6 kg) |
| Shipping Height | 11.06 inches (281.0 mm) |

| | |
|----------------|-------------------------|
| Shipping Width | 18.62 inches (473.0 mm) |
| Shipping Depth | 7.09 inches (180.0 mm) |
| Color | Black |

Conformance

| | |
|-------------------|---------------------------|
| Approvals | UL Listed , cUL Listed |
| Standard warranty | 2 years repair or replace |

Sustainable Offer Status

| | |
|-------|--------------------------|
| RoHS | Compliant |
| REACH | REACH: Contains No SVHCs |