



### Overview

Model Name	Rack PDU, Basic, 0U/1U, 208V, 60A, (3) C19
Includes	Installation guide , Safety guide
Standard Lead Time	Usually in Stock
Product Distribution	Afghanistan , Australia , Bangladesh , Bhutan , Brunei Darussalam , Cambodia , Canada , China , Cook Islands , East Timor , Fiji , Hong Kong , India , Indonesia , KOREA, REPUBLIC OF , Malaysia , Myanmar , Nepal , New Zealand , Papua New Guinea , Philippines , Singapore , Sri Lanka , Taiwan , Thailand , United States , Viet Nam

### Output

Maximum Total Current Draw per Phase	60 A
Output Connections	(3) IEC 320 C19 (Battery Backup)
Overload Protection	Yes

### Input

Nominal Input Voltage	200V , 208V
Input Frequency	50/60 Hz
Regulatory Derated Input Current (North America)	48 A
Input Connections	IEC 309
Cord Length	12 feet (3.66 meters)
Maximum Line Current per phase	60 A
Maximum Input Current per phase	60 A

### Physical

Net Weight	15.22 lbs (6.92 kg)
Maximum Height	1.72 inches (44.0 mm)
Maximum Width	15.28 inches (388.0 mm)
Maximum Depth	4.95 inches (126.0 mm)
Shipping Weight	21.56 lbs (9.81 kg)
Shipping Height	15.55 inches (395.0 mm)
Shipping Width	19.7 inches (500.0 mm)

---

Shipping Depth	7.68 inches (195.0 mm)
----------------	------------------------

---

**Conformance**

---

Approvals	UL Listed , cUL Listed
Standard warranty	2 years repair or replace

---

**Sustainable Offer Status**

---

RoHS	Compliant
REACH	REACH: Contains No SVHCs

---