



Overview

Model Name	Rack PDU Extender, Basic, 2U, 30A, 120V, (12)5-20
Includes	Installation guide , Rack Mounting brackets
Standard Lead Time	Usually in Stock
Product Distribution	Anguilla , Antigua And Barbuda , Argentina , Aruba , Bahamas , Barbados , Belize , Bermuda , Bolivia , Brazil , Canada , Chile , Colombia , Costa Rica , Cuba , Dominica , Dominican Republic , Ecuador , El Salvador , Falkland Islands (Malvinas) , Grenada , Guadeloupe , Guatemala , Guyana , French Guiana , Haiti , Honduras , Jamaica , Madagascar , Martinique , Mauritius , Mayotte , Mexico , Netherlands Antilles , Nicaragua , Panama , Paraguay , Peru , Puerto Rico , Reunion , SAINT KITTS AND NEVIS , SAINT LUCIA , SAINT VINCENT AND THE GRENADINES , Trinidad And Tobago , Turks And Caicos Islands , United States , Uruguay , Venezuela , VIRGIN ISLANDS (UNITED STATES)

Output

Nominal Output Voltage	120V
Maximum Total Current Draw per Phase	24 A
Output Connections	(12) NEMA 5-20R (Battery Backup)

Input

Nominal Input Voltage	200V , 208V
Input Frequency	50/60 Hz
Regulatory Derated Input Current (North America)	24 A
Input Connections	NEMA L14-30P
Cord Length	28 feet (8.53 meters)
Number of Power Cords	1
Maximum Input Current per phase	30 A
Load Capacity	5760 VA

Physical

Net Weight	14.0 lbs (6.36 kg)
Maximum Height	3.5 inches (89.0 mm)
Maximum Width	17.2 inches (437.0 mm)

Maximum Depth	3.5 inches (89.0 mm)
Shipping Weight	16.0 lbs (7.27 kg)
Shipping Height	6.0 inches (152.0 mm)
Shipping Width	20.5 inches (521.0 mm)
Shipping Depth	20.5 inches (521.0 mm)
Color	Black

Environmental

Operating Environment	32 - 113 °F (0 - 45 °C)
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-10000 feet (0-3000 meters)
Storage Temperature	-13 - 149 °F (-25 - 65 °C)
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-50000 feet (0-15000 meters)

Conformance

Approvals	CSA C22.2 No. 107.1 , UL 1778 , UL Listed , cUL Listed
Standard warranty	2 years repair or replace