


# AP7601

Rack PDU,Metered, Zero U, 5.7kW, 120V,  
(42)5-20



AP7601 has not been replaced. Please contact your customer care center for more information.

## Overview

|                      |  |
|----------------------|--|
| Model Name           | Rack PDU,Metered, Zero U, 5.7kW, 120V,(42)5-20   |
| Standard Lead Time   | Usually in Stock   |
| Product Distribution | Anguilla , Antigua And Barbuda , Argentina , Aruba , Barbados , Belize , Bolivia , Brazil , Canada , Chile , Colombia , Costa Rica , Cuba , Dominican Republic , Ecuador , El Salvador , Falkland Islands (Malvinas) , Guatemala , Guyana , Honduras , Jamaica , Japan , Mexico , Netherlands Antilles , Nicaragua , Panama , Paraguay , Peru , Puerto Rico , Trinidad And Tobago , United States , Uruguay , Venezuela , VIRGIN ISLANDS (UNITED STATES) |

## Output

|                                      |                                  |
|--------------------------------------|----------------------------------|
| Nominal Output Voltage               | 120V                             |
| Maximum Total Current Draw per Phase | 16 A                             |
| Output Connections                   | (42) NEMA 5-20R (Battery Backup) |
| Always on Outlets                    | 42                               |
| Overload Protection                  | No                               |

## Input

|                                 |                      |
|---------------------------------|----------------------|
| Nominal Input Voltage           | 208V , 208 3PH       |
| Input Frequency                 | 50/60 Hz             |
| Input Connections               | NEMA L21-20P         |
| Cord Length                     | 3 feet (0.91 meters) |
| Number of Power Cords           | 1                    |
| Acceptable Input Voltage        | 90-253 VAC           |
| Maximum Input Current per phase | 16 A                 |
| Load Capacity                   | 5700 VA              |

## Physical

|                 |                         |
|-----------------|-------------------------|
| Net Weight      | 17.0 lbs (7.74 kg)      |
| Maximum Height  | 60.0 inches (1524.0 mm) |
| Maximum Width   | 3.5 inches (89.0 mm)    |
| Maximum Depth   | 1.76 inches (45.0 mm)   |
| Shipping Weight | 19.0 lbs (8.64 kg)      |
| Shipping Height | 72.0 inches (1829.0 mm) |

|                |                       |
|----------------|-----------------------|
| Shipping Width | 5.0 inches (127.0 mm) |
| Shipping Depth | 4.0 inches (102.0 mm) |
| Color          | Beige                 |

### Environmental

|                             |                               |
|-----------------------------|-------------------------------|
| Operating Environment       | 32 - 104 °F (0 - 40 °C)       |
| Operating Relative Humidity | 0 - 95 %                      |
| Operating Elevation         | 0-10000 feet (0-3000 meters)  |
| Storage Temperature         | 32 - 113 °F (0 - 45 °C)       |
| Storage Relative Humidity   | 0 - 95 %                      |
| Storage Elevation           | 0-50000 feet (0-15000 meters) |

### Conformance

|                   |   |
|-------------------|---|
| Approvals         | DOC/Industry Canada , FCC Part 15 Class A , UL 1950 , UL Listed , VCCI , cUL Listed |
| Standard warranty | 2 years repair or replace   |