

AP7931

Rack PDU, Switched, Zero U, 15A, 100/120V, (16) 5-15



AP7931 has not been replaced. Please contact your customer care center for more information.

⚠ Discontinued

Overview

Model Name	Rack PDU, Switched, Zero U, 15A, 100/120V, (16) 5-15
Includes	Cord retention bracket(s) , Rack Mounting brackets , Toolless Mounting Kit , User Manual
Standard Lead Time	Usually in Stock
Product Distribution	Anguilla , Antigua And Barbuda , Argentina , Aruba , Barbados , Belize , Bermuda , Bolivia , Brazil , Canada , Chile , Colombia , Costa Rica , Cuba , Dominican Republic , Ecuador , El Salvador , Falkland Islands (Malvinas) , Guatemala , Guyana , Honduras , Jamaica , Japan , Mexico , Netherlands Antilles , Nicaragua , Panama , Paraguay , Peru , Puerto Rico , Trinidad And Tobago , United States , Uruguay , Venezuela , VIRGIN ISLANDS (UNITED STATES)

Output

Nominal Output Voltage	120V
Maximum Total Current Draw per Phase	15 A
Output Connections	(16) NEMA 5-15R (Battery Backup)
Overload Protection	No

Input

Nominal Input Voltage	100V , 120V
Input Frequency	50/60 Hz
Regulatory Derated Input Current (North America)	12 A
Input Connections	NEMA 5-15P
Cord Length	10 feet (3.05 meters)
Number of Power Cords	1
Acceptable Input Voltage	100-120 VAC
Maximum Input Current per phase	15 A
Load Capacity	1440 VA

Physical

Net Weight	9.5 lbs (4.32 kg)
Maximum Height	49.0 inches (1245.0 mm)
Maximum Width	2.19 inches (56.0 mm)
Maximum Depth	1.73 inches (44.0 mm)

Shipping Weight	11.5 lbs (5.23 kg)
Shipping Height	84.0 inches (2134.0 mm)
Shipping Width	6.0 inches (152.0 mm)
Shipping Depth	5.0 inches (127.0 mm)
Color	Black

Environmental

Operating Environment	23 - 113 °F (-5 - 45 °C)
Operating Relative Humidity	5 - 95 %
Operating Elevation	0-10000 feet (0-3000 meters)
Storage Temperature	-13 - 149 °F (-25 - 65 °C)
Storage Relative Humidity	5 - 95 %
Storage Elevation	0-50000 feet (0-15000 meters)

Conformance

Approvals	CSA , FCC Part 15 Class A , ICES-003 , Industry Canada , METI Denan , UL 60950 , UL Listed , VCCI , cUL Listed
Standard warranty	2 years repair or replace

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs
Battery Directive	Compliant