



Overview

Description	Free up space and secure power cords between rack-mount PDUs and attached IT equipment with this exclusive easy-to-use cord retention method. While these cords will fit into any standard IEC receptacle or power inlet; the "locking" feature is enabled only when used with APC AP8000 series Rack PDUs or IT equipment with built-in locking receptacles. These locking connectors reduce the probability of accidentally disconnecting cords and dropping loads.
Model Name	Power Cord Kit (6 ea), Locking, C13 to C14, 1.2m, North America
Standard Lead Time	Usually in Stock
Product Distribution	Anguilla , Antigua And Barbuda , Argentina , Aruba , Bahamas , Barbados , Belize , Bermuda , Bolivia , Brazil , Canada , Cayman Islands , Chile , Colombia , Costa Rica , Cuba , Dominica , Dominican Republic , Ecuador , El Salvador , Falkland Islands (Malvinas) , Grenada , Guatemala , Guyana , Haiti , Honduras , Jamaica , Mexico , Netherlands Antilles , Nicaragua , Panama , Paraguay , Peru , Puerto Rico , SAINT KITTS AND NEVIS , SAINT LUCIA , SAINT VINCENT AND THE GRENADINES , Trinidad And Tobago , United States , Uruguay , Venezuela , VIRGIN ISLANDS (UNITED STATES)

Output

Maximum Total Current Draw per Phase	10 A
Output Connections	(1) IEC 320 C13 (Battery Backup)
Cord Length	4

Input

Input Connections	IEC-320 C14
Cord Length	4 feet (1.22 meters)
Number of Power Cords	6
Maximum Line Current per phase	10 A
Maximum Input Current per phase	10 A

Physical

Net Weight	2.23 lbs (1.01 kg)
Maximum Height	9.45 inches (240.0 mm)
Maximum Width	2.76 inches (70.0 mm)
Maximum Depth	1.77 inches (45.0 mm)
Shipping Weight	2.23 lbs (1.01 kg)

Shipping Height	9.45 inches (240.0 mm)
Shipping Width	2.76 inches (70.0 mm)
Shipping Depth	1.77 inches (45.0 mm)
Color	Black

Environmental

Operating Environment	32 - 221 °F (0 - 105 °C)
Operating Relative Humidity	20 - 80 %
Operating Elevation	0-10000 feet (0-3000 meters)
Storage Temperature	-13 - 221 °F (-25 - 105 °C)
Storage Relative Humidity	20 - 80 %
Storage Elevation	0-50000 feet (0-15000 meters)

Conformance

Approvals	CSA , UL Listed
Standard warranty	2 years repair or replace

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs