



### Overview

Model Name	Power Cord Splitter, L21-20P to (3)L6-20R
Standard Lead Time	Usually in Stock
Product Distribution	Canada , Taiwan , United States

### Output

Maximum Total Current Draw per Phase	16 A
Output Connections	(3) NEMA L6-20R (Battery Backup)
Cord Length	2, 4, 6

### Input

Input Frequency	50/60 Hz
Input Connections	NEMA L21-20P
Number of Power Cords	1
Maximum Line Current per phase	20 A
Maximum Input Current per phase	20 A

### Physical

Net Weight	2.26 lbs (1.02 kg)
Shipping Weight	3.0 lbs (1.36 kg)
Shipping Height	3.0 inches (76.0 mm)
Shipping Width	12.5 inches (318.0 mm)
Shipping Depth	12.5 inches (318.0 mm)
Color	Black

### Environmental

Operating Environment	32 - 104 °F (0 - 40 °C)
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-10000 feet (0-3000 meters)
Storage Temperature	32 - 113 °F (0 - 45 °C)

---

Storage Relative Humidity	0 - 95 %
Storage Elevation	0-50000 feet (0-15000 meters)

---

**Conformance**

---

Standard warranty	2 years repair or replace
-------------------	---------------------------

---