



### Overview

Model Name	Battery Management Harness - 25ft
Includes	Installation guide
Standard Lead Time	Usually Ships within 2 Weeks
Product Distribution	Albania , Algeria , Andorra , Angola , Armenia , Australia , Austria , Azerbaijan , Bahrain , Belarus , Belgium , Benin , Bosnia And Herzegovina , Botswana , Bulgaria , Burkina Faso , Burundi , Cambodia , Cameroon , Canada , Cayman Islands , Central African Republic , Chad , Congo , CONGO, THE DEMOCRATIC REPUBLIC OF THE , Cote D'Ivoire , Croatia , Cyprus , Czech Republic , Denmark , Djibouti , Egypt , Equatorial Guinea , Eritrea , Estonia , Ethiopia , Finland , France , Gabon , Gambia , Georgia , Germany , Ghana , Gibraltar , Greece , Guinea , Hungary , Iceland , India , Iran (Islamic Republic Of) , Iraq , Ireland , Israel , Italy , Jordan , Kazakhstan , Kenya , Kuwait , Latvia , Lebanon , Lesotho , Liberia , Liechtenstein , Lithuania , Luxembourg , Macedonia , Malawi , Mali , Malta , Mauritania , Moldova, Republic Of , Mongolia , Morocco , Mozambique , Namibia , Netherlands , New Zealand , Niger , Nigeria , Norway , Oman , Pakistan , Poland , Portugal , Romania , Russian Federation , Rwanda , Saudi Arabia , Senegal , Sierra Leone , Slovakia (Slovak Republic) , Slovenia , Somalia , South Africa , Spain , Sudan , Suriname , Sweden , Switzerland , Tajikistan , TANZANIA, UNITED REPUBLIC OF , Togo , Tunisia , Turkey , Turkmenistan , Uganda , Ukraine , United Arab Emirates , United States , Uzbekistan , Western Sahara , Yemen , Zambia , Zimbabwe

### Physical

Net Weight	7.0 lbs (3.18 kg)
Maximum Height	7.0 inches (178.0 mm)
Maximum Width	11.0 inches (279.0 mm)
Maximum Depth	4.0 inches (102.0 mm)
Shipping Weight	8.0 lbs (3.64 kg)
Shipping Height	10.0 inches (254.0 mm)
Shipping Width	14.0 inches (356.0 mm)
Shipping Depth	6.0 inches (152.0 mm)
Cord Length	25 feet (7.62 meters)

### Environmental

Operating Environment	5 - 113 °F (-15 - 45 °C)
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-30000 feet (0-9000 meters)
Storage Temperature	-4 - 113 °F (-20 - 45 °C)

---

Storage Relative Humidity	0 - 95 %
Storage Elevation	0-30000 feet (0-9000 meters)

---

**Conformance**

---

Standard warranty	2 years repair or replace
-------------------	---------------------------

---