



Price\*\* : 37.40 USD



APN has not been replaced. Please contact your customer care center for more information.

⚠ Discontinued

Main

Range of product	L 100/300
Series name	Severe duty
Product or component type	Limit switch lever
Device short name	L 100/300
Associated complete product	HML 100 HML 300 ML 100 ML 300 L 300 HL 100 L 100 HL 300
Movement of operating head	Rotary
Type of operator	Aluminium spring return roller lever 127.00 mm (5 in) - -
Type of roller	1 nylon center roller 19.05 mm (0.75 in) 6.35 mm (0.25 in)
Type of approach	Lateral approach
Positive opening	Without

Complementary

Switch actuation	By 30° cam
Net weight	0.05 kg (0.1 lb(US))

Environment

Ambient air temperature for operation	-23...85 °C (-10...185 °F)
Ambient air temperature for storage	-23...85 °C (-10...185 °F)
Environmental characteristic	Standard environment

## Ordering and shipping details

Category	21519-9007 MISCELLANEOUS
Discount Schedule	DS1
GTIN	00785901449775
Package weight(Lbs)	1.60 oz (45.359 g)
Returnability	No
Country of origin	MX

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Di-isodecyl phthalate (DIDP) and Diisononyl phthalate (DINP) which is known to the State of California to cause Carcinogen + Reproductive harm. For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

## Contractual warranty

Warranty	18 months
----------	-----------