



### Overview

Model Name	NetShelter VX Seismic 42U Enclosure w/Sides Black
Includes	Doors , Key(s) , Roof , Side Panels , User Manual
Standard Lead Time	Special Order - Call for Quoted Lead Times
Product Distribution	Canada , Japan , United States

### Supported Hardware

Panel Size	0
Brightness	0 nits
Pixel Pitch	0.0
Display Colors	0
LCD Power Consumption	0 W

### Physical

Net Weight	518.0 lbs (235.45 kg)
Maximum Height	81.5 inches (2070.0 mm)
Maximum Width	23.5 inches (597.0 mm)
Maximum Depth	42.2 inches (1072.0 mm)
Shipping Weight	556.0 lbs (252.73 kg)
Shipping Height	87.0 inches (2210.0 mm)
Shipping Width	29.5 inches (749.0 mm)
Shipping Depth	47.5 inches (1207.0 mm)
Minimum Mounting Depth	0.0
Maximum Mounting Depth	36.77
Rack Height	42 U
Color	Black
Units per Pallet	1.0
Vertical Posts	16 gauge
Front Door	16 gauge
Rear Door	16 gauge
Roof	18 gauge
EIA Mounting Rails	14 gauge

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

---

Side Panels	20 gauge
-------------	----------

---

**Environmental**

---

CFM	0
-----	---

---

**Conformance**

---

Approvals	NEBS GR-63-CORE (Seismic Zone 4)
Standard warranty	5 year repair or replace

---