



Overview

Model Name	NetShelter SX 42U 750mm Wide x 1200mm Deep Enclosure Without Sides Without Doors Black
Includes	Baying hardware , Key(s) , Leveling feet , Mounting Hardware , Pre-installed casters
Standard Lead Time	Usually in Stock
Product Distribution	Canada , United States

Supported Hardware

Panel Size	0
Brightness	0 nits
Pixel Pitch	0.0
Display Colors	0
LCD Power Consumption	0 W

Physical

Net Weight	355.0 lbs (161.37 kg) (161.37 kg)
Maximum Height	78.39 inches (1991.0 mm) (1991.0 mm)
Maximum Width	29.53 inches (750.0 mm)
Maximum Depth	47.24 inches (1200.0 mm) (1200.0 mm)
Shipping Weight	403.0 lbs (183.18 kg) (183.18 kg)
Shipping Height	83.39 inches (2118.0 mm) (2118.0 mm)
Shipping Width	33.5 inches (851.0 mm) (851.0 mm)
Shipping Depth	52.5 inches (1334.0 mm) (1334.0 mm)
Minimum Mounting Depth	10.31
Maximum Mounting Depth	41.26
Rack Height	42 U
Color	Black
Units per Pallet	1.0
Vertical Posts	16 gauge
Front Door	0 gauge
Rear Door	0 gauge
Roof	18 gauge
EIA Mounting Rails	14 gauge

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Side Panels	0 gauge
-------------	---------

Environmental

CFM	0
-----	---

Conformance

Approvals	UL 2416 , UL 60950-1
Standard warranty	5 year repair or replace

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs
