

# AR3810

## NetShelter AV 42U 600mm Wide x 825mm Deep Enclosure with Sides and 10-32 Threaded Rails Black



### Overview

Description	Feature-rich enclosure specifically for the professional A/V market and optimized for cable management, power distribution, and airflow management.
Model Name	NetShelter AV 42U 600mm Wide x 825mm Deep Enclosure with Sides and 10-32 Threaded Rails Black
Includes	Documentation CD , Installation guide , Key(s) , Keyed-alike doors and side panels , Leveling feet , Mounting Hardware , Pre-installed casters , Side Panels
Standard Lead Time	Usually in Stock
Product Distribution	Canada , United States

### Physical

Net Weight	263.0 lbs (119.55 kg)
Maximum Height	78.41 inches (1991.0 mm)
Maximum Width	23.62 inches (600.0 mm)
Maximum Depth	32.48 inches (825.0 mm)
Shipping Weight	294.0 lbs (133.64 kg)
Shipping Height	83.5 inches (2121.0 mm)
Shipping Width	29.5 inches (749.0 mm)
Shipping Depth	40.5 inches (1029.0 mm)
Maximum Mounting Depth	26.73
Rack Height	42 U
Color	Black

### Conformance

Approvals	UL 2416 , UL 60950-1
Standard warranty	5 year repair or replace

### Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs