



Overview

Description	Specialized enclosures with integrated cooling, noise dampening, and power distribution for server and network applications in office environments.
Model Name	NetShelter CX 38U in colour Dark Grey
Includes	Casters , Installation guide , Key(s) , Leveling feet , Rack Power Distribution Unit (PDU) , Side Panels
Standard Lead Time	Special Order - Call for Quoted Lead Times
Product Distribution	Anguilla , Antigua And Barbuda , Argentina , Aruba , Bahamas , Barbados , Belize , Bermuda , Bolivia , Brazil , Canada , Cayman Islands , Chile , Colombia , Costa Rica , Cuba , Dominica , Dominican Republic , Ecuador , El Salvador , Falkland Islands (Malvinas) , Grenada , Guatemala , Guyana , Haiti , Honduras , Jamaica , Mexico , Netherlands Antilles , Nicaragua , Panama , Paraguay , Peru , Puerto Rico , SAINT KITTS AND NEVIS , SAINT LUCIA , SAINT VINCENT AND THE GRENADINES , Trinidad And Tobago , United States , Uruguay , Venezuela , VIRGIN ISLANDS (UNITED STATES)

Input

Nominal Input Voltage	115V , 120V
Input Frequency	50/60 Hz
Input Connections	NEMA 5-15P

Physical

Net Weight	446.44 lbs (202.5 kg)
Maximum Height	76.77 inches (1950.0 mm)
Maximum Width	29.53 inches (750.0 mm)
Maximum Depth	44.49 inches (1130.0 mm)
Shipping Weight	507.06 lbs (230.0 kg)
Shipping Height	84.65 inches (2150.0 mm)
Shipping Width	31.5 inches (800.0 mm)
Shipping Depth	47.24 inches (1200.0 mm)
Minimum Mounting Depth	28.35
Maximum Mounting Depth	34.65
Rack Height	38 U
Color	Grey
Units per Pallet	1.0

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Conformance

Approvals	EIA 19 Inch , TAA compliance
Standard warranty	2 year (manufacturer's defect)

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs
