



Overview

Model Name	NetShelter SX 45U 600mm Wide Perforated Split Doors Black
Includes	Door handle , Door mounting hardware , Installation guide , Key(s)
Standard Lead Time	Usually in Stock
Product Distribution	Anguilla , Antigua And Barbuda , Argentina , Aruba , Bahamas , Barbados , Belize , Bermuda , Bolivia , Brazil , Canada , Cayman Islands , Chile , Colombia , Costa Rica , Cuba , Dominica , Dominican Republic , Ecuador , El Salvador , Falkland Islands (Malvinas) , Grenada , Guatemala , Guyana , Haiti , Honduras , Jamaica , Mexico , Netherlands Antilles , Nicaragua , Panama , Paraguay , Peru , Puerto Rico , SAINT KITTS AND NEVIS , SAINT LUCIA , SAINT VINCENT AND THE GRENADINES , Trinidad And Tobago , United States , Uruguay , Venezuela , VIRGIN ISLANDS (UNITED STATES)

Supported Hardware

Panel Size	0
Brightness	0 nits
Pixel Pitch	0.0
Display Colors	0
LCD Power Consumption	0 W

Physical

Net Weight	23.89 lbs (10.86 kg)
Maximum Height	80.47 inches (2044.0 mm)
Maximum Width	23.62 inches (600.0 mm)
Maximum Depth	0.98 inches (25.0 mm)
Shipping Weight	33.66 lbs (15.3 kg)
Shipping Height	84.25 inches (2140.0 mm)
Shipping Width	15.35 inches (390.0 mm)
Shipping Depth	7.87 inches (200.0 mm)
Minimum Mounting Depth	0.0
Maximum Mounting Depth	0.0
Rack Height	0 U
Color	Black
Units per Pallet	0.0
Vertical Posts	0 gauge

Front Door	0 gauge
Rear Door	0 gauge
Roof	0 gauge
EIA Mounting Rails	0 gauge
Side Panels	0 gauge

Environmental

CFM	0
-----	---

Conformance

Standard warranty	2 years repair or replace
-------------------	---------------------------

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs