



AR8381BLK has not been replaced. Please contact your customer care center for more information.

Overview

Model Name	NetShelter VX 25U Roof Black
Includes	Roof mounting hardware
Standard Lead Time	Usually in Stock
Product Distribution	Afghanistan , Albania , Andorra , Anguilla , Antigua And Barbuda , Argentina , Aruba , Australia , Austria , Bangladesh , Barbados , Belgium , Belize , Bermuda , Bhutan , Bolivia , Brazil , Brunei Darussalam , Canada , Cayman Islands , Chile , China , Colombia , Cook Islands , Costa Rica , Cuba , Cyprus , Czech Republic , Denmark , Dominican Republic , East Timor , Ecuador , El Salvador , Estonia , Falkland Islands (Malvinas) , Fiji , Finland , France , Germany , Greece , Guatemala , Guyana , Honduras , Hong Kong , Hungary , Iceland , India , Indonesia , Ireland , Italy , Jamaica , KOREA, REPUBLIC OF , Latvia , Liechtenstein , Lithuania , Luxembourg , Macedonia , Malaysia , Malta , Mexico , Myanmar , Nepal , Netherlands , Netherlands Antilles , New Zealand , Nicaragua , Norway , Pakistan , Panama , Papua New Guinea , Paraguay , Peru , Philippines , Poland , Portugal , Puerto Rico , Singapore , Slovakia (Slovak Republic) , Slovenia , Spain , Sri Lanka , Sweden , Switzerland , Taiwan , Thailand , Trinidad And Tobago , United States , Uruguay , Venezuela , Viet Nam , VIRGIN ISLANDS (UNITED STATES)

Physical

Net Weight	13.0 lbs (5.91 kg)
Maximum Height	2.0 inches (51.0 mm)
Maximum Width	23.0 inches (584.0 mm)
Maximum Depth	42.0 inches (1067.0 mm)
Shipping Weight	19.0 lbs (8.64 kg)
Shipping Height	4.0 inches (102.0 mm)
Shipping Width	23.5 inches (597.0 mm)
Shipping Depth	43.5 inches (1105.0 mm)
Color	Black

Conformance

Standard warranty	2 years repair or replace
-------------------	---------------------------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications