



Overview

| | |
|----------------------|---|
| Description | This 10" wide, high capacity vertical cable manager for 2 and 4 Post open frame racks features a single-sided cable channel with multiple internal cable tie-off locations and smooth plastic fingers at 1U increments for organized patching applications. |
| Model Name | Performance, Vertical Cable Manager for 2 & 4 Post Racks, 84"H x 10"W, Single-Sided with Door |
| Includes | Doors |
| Standard Lead Time | Usually in Stock |
| Product Distribution | Anguilla |

Physical

| | |
|-----------------|--------------------------|
| Net Weight | 64.91 lbs (29.5 kg) |
| Maximum Height | 84.02 inches (2134.0 mm) |
| Maximum Width | 9.97 inches (253.0 mm) |
| Maximum Depth | 14.17 inches (360.0 mm) |
| Shipping Weight | 77.88 lbs (35.4 kg) |
| Shipping Height | 13.82 inches (351.0 mm) |
| Shipping Width | 21.26 inches (540.0 mm) |
| Shipping Depth | 89.76 inches (2280.0 mm) |
| Color | Black |

Conformance

| | |
|-------------------|---------------------------|
| Approvals | UL Listed |
| Standard warranty | 2 years repair or replace |

Sustainable Offer Status

| | |
|-------|--------------------------|
| RoHS | Compliant |
| REACH | REACH: Contains No SVHCs |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications