

Product data sheet

Specifications



SPEEDDRIVE,20HP,230V,ATV71 + conduit box

ATV71HD15M3XT1

-  **Discontinued on:** Sep 9, 2021
-  **To be end-of-service on:** Dec 31, 2026

 **Discontinued**

Main

Asynchronous Motor Control Profile	Constant torque standard
Device Short Name	ATV71
Range Of Product	Altivar 71

Complementary

Line Rated Current	66 A
Cable Entry	Type 1 conduit entry outdoor
Communication Port Protocol	CANopen Modbus
Input Voltage	208/240 V AC
Keypad Type	LCD keypad
Maximum Horse Power Rating	20 hp
Motor Power Kw	15 kW
Phase	3 phase input 3 phase output
Output Voltage	<= rated supply voltage

Environment

Emc Filter	Without EMC filter
Ip Degree Of Protection	IP20
Nema Degree Of Protection	No enclosure rating (open device)
Protective Treatment	None

Ordering and shipping details

Category	22131-ATV71 - 7.5 THRU 50HP
Discount Schedule	CP4C
Returnability	No
Country Of Origin	ID

Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications