

Product data sheet

Specifications



SPEEDDRIVE,40HP,230V,ATV71 + conduit box

ATV71HD30M3XT1

⚠ Discontinued on: Sep 9, 2021

⚠ To be end-of-service on: Dec 31, 2026

⚠ Discontinued

Main

Asynchronous Motor Control Profile	Constant torque standard
Device Short Name	ATV71
Range Of Product	Altivar 71

Complementary

Line Rated Current	120 A
Cable Entry	Type 1 conduit entry outdoor
Communication Port Protocol	Modbus CANopen
Input Voltage	208/240 V AC
Keypad Type	LCD keypad
Maximum Horse Power Rating	40 hp
Motor Power Kw	30 kW
Phase	3 phase output 1 phase input
Output Voltage	<= rated supply voltage

Environment

Emc Filter	Without EMC filter
Ip Degree Of Protection	IP20
Nema Degree Of Protection	No enclosure rating (open device)
Protective Treatment	None

Ordering and shipping details

Category	22131-ATV71 - 7.5 THRU 50HP
Discount Schedule	CP4C
Returnability	No
Country Of Origin	CN

Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications