

# Product data sheet

Specifications



## SPEEDDRIVE,60HP,460V,ATV71 + conduit box

ATV71HD45N4T1

⚠ Discontinued on: Sep 9, 2021

⚠ To be end-of-service on: Dec 31, 2026

⚠ Discontinued

### Main

Asynchronous Motor Control Profile	Constant torque standard
Device Short Name	ATV71
Range Of Product	Altivar 71

### Complementary

Line Rated Current	94 A
Cable Entry	Type 1 conduit entry outdoor
Communication Port Protocol	Modbus CANopen
Input Voltage	400/480 V AC
Keypad Type	LCD keypad
Maximum Horse Power Rating	60 hp
Motor Power Kw	45 kW
Phase	3 phase input 3 phase output
Output Voltage	<= rated supply voltage

### Environment

Emc Filter	Class A EMC filter integrated
Ip Degree Of Protection	IP20
Nema Degree Of Protection	No enclosure rating (open device)
Protective Treatment	None

### Ordering and shipping details

Category	22132-ATV71 - 60 THRU 150HP DRIVES
Discount Schedule	CP4C
Returnability	No
Country Of Origin	CN

### Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications