

Product data sheet

Specifications



SPEEDDRIVE,3HP,460V,ATV71 + conduit box

ATV71HU22N4T1

⚠ Discontinued on: Sep 9, 2021

⚠ To be end-of-service on: Dec 31, 2026

⚠ Discontinued

Main

Asynchronous Motor Control Profile	Constant torque standard
Device Short Name	ATV71
Range Of Product	Altivar 71

Complementary

Line Rated Current	5.8 A
Cable Entry	Type 1 conduit entry outdoor
Communication Port Protocol	CANopen Modbus
Input Voltage	400/480 V AC
Keypad Type	LCD keypad
Maximum Horse Power Rating	3 hp
Motor Power Kw	2.2 kW
Phase	3 phase input 3 phase output
Output Voltage	<= rated supply voltage

Environment

Emc Filter	Class A EMC filter integrated
Ip Degree Of Protection	IP20
Nema Degree Of Protection	No enclosure rating (open device)
Protective Treatment	None

Ordering and shipping details

Category	22130-ATV71 - 1/2 THRU 5HP DRIVES
Discount Schedule	CP4C
Returnability	No
Country Of Origin	ID

Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications