

# Product data sheet

Specifications



## SPEEDDRIVE,4HP,230V,ATV71 + conduit box

ATV71HU30M3T1

 **Discontinued on:** Nov 9, 2021

 **Discontinued**

### Main

Asynchronous Motor Control Profile	Constant torque standard
Device Short Name	ATV71
Range Of Product	Altivar 71

### Complementary

Line Rated Current	13.7 A 11 A 1 phase
Cable Entry	Type 1 conduit entry outdoor
Communication Port Protocol	Modbus CANopen
Input Voltage	208/240 V AC
Keypad Type	LCD keypad
Maximum Horse Power Rating	4 hp 3 hp, 1 phase
Motor Power Kw	3 kW 2.2 kW, 1 phase
Phase	3 phase output 1 phase input 3 phase
Output Voltage	<= rated supply voltage

### Environment

Emc Filter	Class A EMC filter integrated
Ip Degree Of Protection	IP20
Nema Degree Of Protection	No enclosure rating (open device)
Protective Treatment	None

### Ordering and shipping details

Category	22130-ATV71 - 1/2 THRU 5HP DRIVES
Discount Schedule	CP4C
Returnability	No

### Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

