
# Product data sheet

Specifications





Cable end, Linergy TR cable ends, twin conductor, grey, 2.5mmÅ<sup>2</sup>, for insulated cable, medium size, 5 sets of 50

AZ5DE025

Product availability: Non-Stock - Not normally stocked in distribution facility

### Price\*: 0.32 USD

### Main

Range Of Product	Linergy
Product Or Component Type	Cable end
Cable End Size	Medium
Standards	NF C 63-023
Type Of Packing	Dispenser pack
Quantity Per Set	5 sets of 50
Cable Cross Section	0.00 in² (2.5 mm²)

### Complementary

· · · · · · · · · · · · · · · · · ·	
Cable End Type	Twin conductor
Additional Information	Without marker tag holder
Color	Gray
Bezel Material	Halogen-free plastic
Tube Material	Copper ISO 1337
Number Of Cables	2
Awg Gauge	AWG 14
Bezel Size	Ø 4.2 x 7.8 mm
Tube Diameter	0.13 in (3.2 mm)
Length	0.73 in (18.5 mm)
Tube Length	0.39 in (10 mm)
Net Weight	0.32 lb(US) (0.145 kg)

### Environment

Product Certifications	cCSAus
Ambient Air Temperature For Operation	-4221 °F (-20105 °C)

## Ordering and shipping details

Category	US1000l22621
Discount Schedule	0001

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Gtin	3389110515893
Returnability	No
Country Of Origin	US

# **Packing Units**

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.16 in (0.400 cm)
Package 1 Width	0.16 in (0.400 cm)
Package 1 Length	0.79 in (2.000 cm)
Package 1 Weight	0.02 oz (0.500 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	250
Package 2 Height	5.12 in (13.000 cm)
Package 2 Width	2.76 in (7.000 cm)
Package 2 Length	4.96 in (12.600 cm)
Package 2 Weight	4.44 oz (126.000 g)
Unit Type Of Package 3	S04
Number Of Units In Package 3	10000
Package 3 Height	11.81 in (30.000 cm)
Package 3 Width	15.75 in (40.000 cm)
Package 3 Length	23.62 in (60.000 cm)
Package 3 Weight	14.09 lb(US) (6.392 kg)

### **Contractual warranty**

Warranty

18 months

# Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

### Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Pvc Free
Halogen Free Plastic Parts Product

### **Certifications & Standards**

Circularity Profile	No need of specific recycling operations
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Reach Regulation	REACh Declaration