Product data sheet

Specification





Lexium 28

servo motor BCH, Lexium 28, 60mm, 200W, 0.17kg.cm², with oil seal, with key, brake, leads connection

BCH2LD0233CF5C

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 796.68 USD

Main

Range Compatibility

Product Or Component Type	Servo motor	
Device Short Name	BCH2	
Complementary		
Maximum Mechanical Speed	5000 rpm	
[Us] Rated Supply Voltage	220 V 110 V	
Phase	Three phase Single phase	
Continuous Stall Current	1.11 A	
Continuous Stall Torque	5.66 lbf.in (0.64 N.m) LXM26D 1.5 A, 220 V, single phase 5.66 lbf.in (0.64 N.m) LXM26D 1.5 A, 220 V, three phase 5.66 lbf.in (0.64 N.m) LXM28 1.5 A, 220 V, single phase 5.66 lbf.in (0.64 N.m) LXM28 1.5 A, 220 V, three phase 5.66 lbf.in (0.64 N.m) LXM28 3.6 A, 110 V, single phase	
Continuous Power	200 W	
Peak Stall Torque	16.99 lbf.in (1.92 N.m) LXM26D 1.5 A, 220 V, single phase 16.99 lbf.in (1.92 N.m) LXM26D 1.5 A, 220 V, three phase 16.99 lbf.in (1.92 N.m) LXM28 1.5 A, 220 V, single phase 16.99 lbf.in (1.92 N.m) LXM28 1.5 A, 220 V, three phase 16.99 lbf.in (1.92 N.m) LXM28 3.6 A, 110 V, single phase	
Nominal Output Power	200 W LXM26D 1.5 A, 220 V, single phase 200 W LXM26D 1.5 A, 220 V, three phase 200 W LXM28 1.5 A, 220 V, single phase 200 W LXM28 1.5 A, 220 V, three phase 200 W LXM28 3.6 A, 110 V, single phase	
Nominal Torque	5.66 lbf.in (0.64 N.m) LXM26D 1.5 A, 220 V, single phase 5.66 lbf.in (0.64 N.m) LXM26D 1.5 A, 220 V, three phase 5.66 lbf.in (0.64 N.m) LXM28 1.5 A, 220 V, single phase 5.66 lbf.in (0.64 N.m) LXM28 1.5 A, 220 V, three phase 5.66 lbf.in (0.64 N.m) LXM28 3.6 A, 110 V, single phase	
Nominal Speed	3000 rpm LXM26D 1.5 A, 220 V, single phase 3000 rpm LXM26D 1.5 A, 220 V, three phase 3000 rpm LXM28 1.5 A, 220 V, single phase 3000 rpm LXM28 1.5 A, 220 V, three phase 3000 rpm LXM28 3.6 A, 110 V, single phase	
Maximum Current Irms	4.31 A LXM28 0.2 kW, 220 V 4.31 A LXM28 0.2 kW, 110 V	
Maximum Permanent Current	1.3 A	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Product Compatibility	LXM26D servo drive 0.2 kW, 220 V, single phase LXM26D servo drive 0.2 kW, 220 V, three phase LXM28 servo drive 0.2 kW, 220 V, single phase LXM28 servo drive 0.2 kW, 220 V, three phase LXM28 servo drive 0.2 kW, 110 V, single phase
Shaft End	Keyed
Shaft Diameter	0.55 in (14 mm)
Shaft Length	1.18 in (30 mm)
Key Width	0.20 in (5 mm)
Feedback Type	20 bits single turn absolute encoder
Holding Brake	With
Holding Torque	11.51 lbf.in (1.3 N.m) built-in
Mounting Support	Asian standard flange
Motor Flange Size	2.36 in (60 mm)
Electrical Connection	Free lead
Torque Constant	0.58 N.m/A 68 °F (20 °C)
Back Emf Constant	35 V/krpm 68 °F (20 °C)
Rotor Inertia	0.17 kg.cm ²
Stator Resistance	12.2 Ohm 68 °F (20 °C)
Stator Inductance	22.5 mH 68 °F (20 °C)
Stator Electrical Time Constant	1.84 ms 68 °F (20 °C)
Maximum Radial Force Fr	200 N 3000 rpm
Maximum Axial Force Fa	70 N
Brake Pull-In Power	11.2 W
Type Of Cooling	Natural convection
Length	5.51 in (140 mm)
Number Of Motor Stacks	1
Centring Collar Diameter	1.97 in (50 mm)
Centring Collar Depth	0.22 in (5.5 mm)
Number Of Mounting Holes	4
Mounting Holes Diameter	0.22 in (5.5 mm)
Circle Diameter Of The Mounting Holes	2.76 in (70 mm)
Distance Shaft Shoulder-Flange	0.22 in (5.5 mm)
Net Weight	3.31 lb(US) (1.5 kg)

Environment

Ip Degree Of Protection	IP50 IM V3 IP65 IM B5, IM V1
Ambient Air Temperature For Operation	32104 °F (040 °C)

Ordering and shipping details

Category	US1PC5318281
Discount Schedule	PC53

Gtin	3606480733550
Returnability	No
Country Of Origin	CN

Packing Units

r doming office	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.37 in (11.1 cm)
Package 1 Width	5.71 in (14.5 cm)
Package 1 Length	10.43 in (26.5 cm)
Package 1 Weight	4.59 lb(US) (2.08 kg)
Unit Type Of Package 2	CAR
Number Of Units In Package 2	5
Package 2 Height	11.81 in (30 cm)
Package 2 Width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)
Package 2 Weight	25.10 lb(US) (11.387 kg)
Unit Type Of Package 3	PAL
Number Of Units In Package 3	40
Package 3 Height	23.62 in (60 cm)
Package 3 Width	23.62 in (60 cm)
Package 3 Length	31.50 in (80 cm)
Package 3 Weight	200.83 lb(US) (91.096 kg)



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
②	Mercury Free	
②	Rohs Exemption Information Yes	
⊘	Pvc Free	


Certifications & Standards

Reach Regulation	REACh Declaration	
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)	
China Rohs Regulation	China RoHS declaration	
Environmental Disclosure	Product Environmental Profile	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.	
Circularity Profile	End of Life Information	
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov	

Dimensions Drawings

Dimensions

Dimensions of Motor




	mm	in.
L (without holding brake)	104	4.09
L (with holding brake)	140	5.51
Z	57	2.24

Performance Curves

Torque/Speed Curves with 230 V Single/Three Phase Supply Voltage

Servo Motor with LXM28AU02●●● Servo Drive M [Nm]



- 1: Peak torque
- 2: Continuous torque